

USER'S MANUAL


T204
T210



Thank you for purchasing our product. Before first use, read this instruction manual carefully and keep it for future reference.

WIRES CONNECTION

Power amplifier for schematic diagram.



- Adjust the matching Impedance of the Power Amplifie.
- Click the picture to connect the positive and negative poles of the horn to the power Amplifie.

SPECIFICATION

	T204	T210
Diameter	20.5 cm	25.5 cm
Max. power	80(W)	120(W)
Impedance	8 Ohm	8 Ohm
Sensitivity	89 dB	90 dB
Frequency response	80-20000Hz	60-20000Hz
Magnet	8 oz	10 oz
Membrane	PP	PP
Voice coil	2.5cm	2.5cm
Suspension	Rubber	Rubber

 English
Correct Disposal of This Product
(Waste Electrical & Electronic Equipment)

(Applicable in the European Union and other European countries with separate collection systems) This marking shown on the product or its literature, indicates that it should not be disposed with other household wastes at the end of its working life. To prevent possible harm to the environment or human health from uncontrolled waste disposal, please separate this from other types of wastes and recycle it responsibly to promote the sustainable reuse of material resources. Household users should contact either the retailer where they purchased this product, or their local government office, for details of where and how they can take this item for environmentally safe recycling. Business users should contact their supplier and check the terms and conditions of the purchase contract. This product should not be mixed with other commercial wastes for disposal.

